



Substation - Aluminum Bolted T Connector

By Burndy
Catalog # [NNT22A19A75](#)

Substation Connectors



Features

- Type NNT Aluminum T-Connectors for Aluminum and Copper Tube to Tube
- Properly proportioned to permit use on copper-aluminum conductor combinations
- Captured hex head bolts permit one-wrench installation

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Tube Std Run Range	4 IPS
Conductor - AL Tube Std Run	4 IPS
Conductor - AL Tube Std Tap Range	2 1/2 IPS
Conductor - AL Tube Std Tap	2 1/2 IPS
Conductor Type	• AL Tube Std-Run • AL Tube Std-Tap

Configuration

Physical Attribute - Pad Orientation	75 Degree
--------------------------------------	-----------

Connector Type	T-Connector
----------------	-------------

Dimensions

Dimension - Height mm	139.7 mm
Dimension - Height inch	5.50 in
Dimension - Width mm	127 mm
Dimension - Width inch	5.00 in
Dimension - L Length Overall mm	295 mm
Dimension - B Length inch	6.00 in
Dimension - Length BB inch	4.50 in
Dimension - Length Overall inch	11.62 in

General

Plated	N
Material - Hardware	Aluminum
UPC	781810159118
Type	Bolted Tees
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810159118
UPC 14 Digit GTIN	00781810159118

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)