



Full Cycle Ratchet Hand Crimper, #26-#8 AWG

By Burndy
Catalog # [M8ND](#)

Full Cycle Ratchet Hand Crimper, #26-#8 AWG Terminals & Splices,
Uses N Dies

Features

- Fully protected ratchet mechanism
- Reinforced heavy duty back
- Long handles provide greater mechanical advantages
- Uses all standard BURNDY N-dies
- Easy groove identification with color-coded dies

Application

Crimping

Specifications

Standards - RoHS Compliance EX
Status

Dimensions

Package Height	0.000 in
Length	10.75 in
Package Weight	0.000 lb.
Dimension - Width inch	1-3/4 in
Package Length	0.000 in
Package Width	0.000 in

Weight	1.75 lb.
Height	2 in
Width	1 in
Dimension - Thread Size	-
Dimension - Length Overall inch	10.75 in
Dimensions	10.75 in x 1 in x 2 in

General

Application - For Use On	#26-8 AWG Terminals and Splices
Trade Name	HYTOOL™
Tool Type	Full Cycle Ratchet Crimper
Product Type	Ratchet and Small Hand Tools
Die Type	N Die
UPC	781810029817
UPC 12 Digit	781810029817
UPC 14 Digit GTIN	00781810029817

Logistics

Package Contents	Tool only
------------------	-----------

Product Assets

[Catalog \[English\]](#)