



Full Cycle Ratchet Crimper for Nuclear Applications, #22 AWG-10 AWG

By Burndy
Catalog # [MR10G6](#)



Full Cycle Ratchet Crimper, Nuclear, #22-10 AWG.

Features

- Long handles provide greater mechanical advantage
- Adjustable stop for terminals (lowers for splices)
- Color-coded die grooves
- Fully protected ratchet mechanism
- Reinforced heavy duty back
- High strength aluminum body

Application

Crimping

General

Application - For Use On	Nylon Insulated Terminals
Catalog Number	MR10G6
Die Type	Permanent Die Grooves
Tool Type	Hand Operated Crimper
Trade Name	HYTOOL™
Type	Crimper
UPC	781810029961
UPC 14 Digit GTIN	00781810029961

Dimensions

Dimensions	11.15 in x 3.00 in x 0.88 in
Height	0.88 in
Length	11.15 in
Width	3 in

Conductor Related

Crimping Ranges	#22 - #10 AWG
-----------------	---------------

Certifications And Compliance

Standards - RoHS Compliance	EX
Status	

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_MR10G6_LineArt](#)
- [Sales Drawings - 30004893](#)
- [Specifications - MR10G6](#)