



Full Cycle Ratchet Crimper, #8-18 AN
Copper #10-22 Sol, #8-22 Str

By Burndy
Catalog # [MR89Q](#)

Full Cycle Ratchet, #8-18 AN CU, YAV/YSV

Features

- Long handles provide greater mechanical advantage
- Adjustable stop for terminals (lowers for splices)
- Color-coded die grooves
- Fully protected ratchet mechanism
- Reinforced heavy duty back
- High strength aluminum body

Application

Crimping

Specifications

EU RoHS Indicator	Yes
Standards - RoHS Compliance	EX
Status	
Buy America(n) Qualified	Contact Manufacturer

Conductor

Crimping Ranges	#18 - #8 AN, #22 - #8 AWG
-----------------	---------------------------

Dimensions

Length	11 in
--------	-------

Width	2.76 in
Weight	1.5 lb.
Height	0.88 in
Dimensions	11 in x 2.76 in x 0.88 in

General

Trade Name	HYTOOL™
Application - For Use On	Uninsulated Terminals and Splices
Type	Crimper
UPC 12 Digit	781810786031
UPC 14 Digit GTIN	00781810786031
Tool Type	Full Cycle Ratchet Crimper
UPC	781810786031
Die Type	Permanent Die Grooves

Logistics

Package Contents	Tool only
Minimum Pack Quantity	1

Product Assets

[Catalog \[English\]](#)