



Mechanical Rotating Crimper, #8 AWG - #4/0 AWG AL

By Burndy
Catalog # [MRC840AL](#)

Mechanical Rotating Crimper, #8 AWG - #4/0 AWG Aluminum Bare
Terminals & Splices

Features

- Spring loaded mechanism locks die wheel into position
- Press mechanism to release
- Rotating die wheel color coded marked with AWG sizes
- Steel jaws

Application

Crimping

Specifications

Standards - RoHS Compliance EX
Status

Conductor

Crimping Ranges Aluminum: #8 AWG - #4/0 AWG

Dimensions

Package Height 0.000 in
Length 26 in
Package Weight 0.000 lb.
Package Length 0.000 in
Package Width 0.000 in



Weight 9.14 lb.
Height 1.5 in
Width 8 in
Dimensions 26 in x 8 in x 1.5 in

General

Application - For Use On Aluminum Terminals and Splices
Trade Name HYTOOL™
Tool Type Mechanical Rotating Crimper
Product Type MRC Series
Die Type Rotating Die Wheel
UPC 781810492840
Type Crimper
UPC 12 Digit 781810492840
UPC 14 Digit GTIN 00781810492840

Logistics

Package Contents Tool only

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)