


Substation - Connector

By Burndy
Catalog # [NS19A19AGS](#)

Substation Connectors



Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Tube Std Run Range	2 1/2 IPS
Conductor - AL Tube Std Run	2 1/2 IPS
Conductor - Connection Combination	Tube to Tube
Conductor - AL Tube Std Tap Range	2 1/2 IPS
Conductor - AL Tube Std Tap	2 1/2 IPS
Conductor Type	• AL Tube Std-Size • CU Tube Std-Size

Configuration

Physical Attribute - Pad Orientation	Straight
Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Number of Run Conductors	1
Connector Type	Couplers

Dimensions

Dimension - Height mm	108.2 mm
Dimension - Height inch	4.26 in
Dimension - Width mm	127 mm
Dimension - Width inch	5.00 in
Dimension - L Length Overall mm	236 mm
Dimension - Length Overall inch	9.31 in

Force Related

Installation Torque	660 LBS/in
Recommended in-lb	

General

Plated	N
Material - Hardware	Aluminum
One Wrench Installation	Y
UPC	621945027565
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	621945027565
UPC 14 Digit GTIN	00621945027565

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)