



Full Cycle Ratchet Crimper, #22-#10 Bare

By Burndy
Catalog # [MRE1022B](#)



Ergo Full Cycle Ratchet Crimper, #22-#10 AWG Uninsulated Terminals & Splices

Features

- Ratchet mechanism does not allow handles to open until full cycle is complete
- Stop plate ensures proper location for consistent reliable connection
- Die Inspection Gauges available (sold separately)
- Easy groove identification with color coded dies
- Ratchet release lever in case of misalignment

Application

Crimping

Specifications

Standards - RoHS Compliance	EX
Status	
Buy American Compliant	No

Conductor

Crimping Ranges	Copper: #22 AWG - #10 AWG
-----------------	---------------------------

Dimensions

Package Height	0.000 in
Length	10.38 in
Package Weight	0.000 lb.
Package Length	0.000 in

Package Width	0.000 in
Weight	1.3 lb.
Height	1 in
Width	3 in
Dimensions	10.38 in x 3 in x 1 in

General

Application - For Use On	Uninsulated Terminals and Splices
Trade Name	HYTOOL™
Sub Brand	HYTOOL
Tool Type	Full Cycle Ratchet Crimper
Product Type	MRE Series
Die Type	Permanent Die Grooves
UPC	781810512982
UPC 12 Digit	781810512982
UPC 14 Digit GTIN	00781810512982

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

- [Catalog \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)