



Full Cycle Ratchet Crimper, #22-10 AWG, Nylon & Vinyl

By Burndy
Catalog # [MRE1022NV](#)



Ergo Full Cycle Ratchet Crimper, #22-#10 AWG Nylon & Vinyl Insulated Conn

Features

- Ratchet mechanism does not allow handles to open until full cycle is complete
- Stop plate ensures proper location for consistent reliable connection
- Die Inspection Gauges available (sold separately)
- Easy groove identification with color coded dies
- Ratchet release lever in case of misalignment

Application

Crimping

Specifications

Standards - RoHS Compliance EX
Status

Conductor

Crimping Ranges Copper: #22 AWG - #10 AWG

Dimensions

Length 10.68 in
Weight 1.3 lb.

Height 1 in
Width 3 in
Dimensions 10.68 in x 3 in x 1 in

General

Application - For Use On Nylon and Vinyl Insulated Terminals and Splices
Trade Name HYTOOL™
Tool Type Full Cycle Ratchet Crimper
Product Type MRE Series
Die Type Permanent Die Grooves
UPC 781810512999
UPC 12 Digit 781810512999
UPC 14 Digit GTIN 00781810512999

Logistics

Package Contents Tool only

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)