

Substation - Copper Coupler - Straight

By Burndy
Catalog # [NS2020](#)

Cast Cu Alloy Bolted Coupler, Cu Tube to Tube, 3" IPS, Silicon Bronze H/W



Features

- Type NS Copper Bolted Coupler, for Copper Straight Tube to Tube
- High copper alloy coupler for joining equal sizes of tube end to end
- Slots between bolts provide independent high pressure areas of contact
- One-wrench installation

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Connection Combination	Tube to Tube
Conductor - Copper Tube Std Tap	3 IPS
Conductor Type	CU Tube Std-Size
Conductor - Copper Tube Std Run	3 IPS
Conductor - Copper Tube Std Size Range	3 IPS
Conductor - Copper Tube Std Size	3 IPS

Configuration

Physical Attribute - Pad Orientation	Straight
--------------------------------------	----------

Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Number of Run Conductors	1
Connector Type	Couplers

Dimensions

Dimension - Height mm	117.6 mm
Dimension - Height inch	4.63 in
Dimension - Width mm	157 mm
Dimension - Width inch	6.19 in
Dimension - L Length Overall mm	184 mm
Dimension - B Length inch	3.63 in
Dimension - Length BB inch	3.63 in
Dimension - Length Overall inch	7.25 in

Force Related

Installation Torque Recommended in-lb	660 LBS/in
---------------------------------------	------------

General

Plated	N
Material - Hardware	Silicon Bronze
One Wrench Installation	Y
UPC	781810002575
Type	Tube to Tube Couplers
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810002575
UPC 14 Digit GTIN	00781810002575

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)