


Substation - Copper Stud Connector

By Burndy
Catalog # [N11DR6544T12](#)

Copper Stud Connectors



Features

- High copper alloy stud connector allows bolting (2) cables to equipment Studs
- Cable orientation is either flag or in-line to the stud

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - Connection Combination	Stud to Tube
Conductor - Copper Solid Size Range	2 AWG-4/0 AWG
Conductor Spacing	1.75 in
Conductor - Copper Str Size Range	2 AWG-1000 kcmil
Conductor - Copper Str Size	• 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil

- 700 kcmil
 - 750 kcmil
 - 800 kcmil
 - 850 kcmil
 - 900 kcmil
 - 1000 kcmil
- 3/8 IPS IPS-3/4 IPS IPS
- 3/8 IPS IPS
 - 1/2 IPS IPS
 - 3/4 IPS IPS

Conductor - Copper Tube Std Size Range

Conductor - Copper Tube Std Size

Configuration

Physical Attribute - Number of Tap Conductors	2
Connector Type	Stud Connector

Dimensions

Dimension - Pin Diameter inch	1.00 in
Dimension - Pin Diameter fraction	1 in
Package Height	0.000 in
Dimension - Height mm	127 mm
Dimension - Height inch	5.00 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - AA Pad Orientation	• 90 Degree • In-line
Package Width	0.000 in
Dimension - L Length Overall mm	121 mm
Dimension - B Length inch	1.53 in
Dimension - Threads per inch	12
Dimension - Length Overall inch	4.78 in

General

Plated	N
Material - Hardware UPC	DURIUM™ Silicon Bronze 781810416839
Type	Studs
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810416839
UPC 14 Digit GTIN	00781810416839

Logistics

Minimum Pack Quantity	2
Pallet Quantity	1

Carton Quantity1

Product Assets

[Catalog \[English\]](#)



A Hubbell brand