




Substation - Copper Stud Connector

By Burndy
Catalog # [N11DR65544T12](#)

Copper Stud Connectors



Features

- High copper alloy stud connector allows bolting (2) cables to equipment Studs
- Cable orientation is either flag or in-line to the stud

Application

Substation

Specifications

Standards - RoHS Compliance	EX
Status	
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - Copper Solid Size Range	1 AWG-4/0 AWG
Conductor - Copper Str Size Range	2 AWG-1000 kcmil
Conductor - Copper Str Size	• 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil

- 550 kcmil
- 600 kcmil
- 700 kcmil
- 750 kcmil
- 800 kcmil
- 850 kcmil
- 900 kcmil
- 1000 kcmil

Configuration

Connector Type	Stud Connector
----------------	----------------

Dimensions

Dimension - Pin Diameter inch	1.125 in
Dimension - Pin Diameter fraction	1-1/8 in
Dimension - Height mm	0 mm
Dimension - Threads per inch	12

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810282687
Type	Studs
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810282687
UPC 14 Digit GTIN	00781810282687

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)



A Hubbell brand