



N2AH4434N, Substation - Copper Terminal

By Burndy

Catalog # [N2AH4434N](#)

Substation Connectors



Features

- Type N2AH Bolted Terminals for 2 Copper Cables to Pad
- High copper alloy reversible cap terminal for joining a wide range of cables to pads
- Tongue is side formed to provide adequate clearance
- Terminal is designed for one-wrench installation

Application

Substation

Specifications

Standards - RoHS Compliance	EX
Status	
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	4/0 AWG
Number Of Conductors	2
Conductor - Connection Combination	Cable to Flat
Conductor - Copper Solid Size Range	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG-1000 kcmil
Conductor - Copper Str Size	• 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil • 700 kcmil • 750 kcmil • 800 kcmil • 850 kcmil • 900 kcmil • 1000 kcmil

Configuration

Physical Attribute - Pad Orientation	Offset
Physical Attribute - Pad Configuration	3 x 3 - 4 holes



A Hubbell brand

Connector Type

Terminal

Dimensions

Dimension - Pad Width inch	3.00 in
Package Height	0.000 in
Dimension - Height mm	66.5 mm
Dimension - Hole Size fraction	9/16
Physical Attribute - Tongue Angle	45 Degree
Dimension - Height inch	2.62 in
Package Weight	0.000 lb.
Dimension - Width mm	155 mm
Dimension - Width inch	6.12 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	162 mm
Dimension - B Length inch	2.88 in
Dimension - D inch	3.00 in
Dimension - N inch	0.62 in
Dimension - Length Overall inch	6.38 in

Force Related

Installation Torque	480
Recommended in-lb	

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
UPC	781810163917
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810163917
UPC 14 Digit GTIN	00781810163917

Logistics

Minimum Pack Quantity	1
Pallet Quantity	300
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)