




Substation - Connector

By Burndy
Catalog # [NYT2826](#)

Substation Connectors



Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	4/0 AWG
Conductor - Copper Str Run	4/0 AWG
Conductor - Connection Combination	Cable to Cable
Conductor Type	• CU C Str-Run • CU C Str-Tap
Conductor - Copper Str Tap Range	2/0 AWG
Conductor - Copper Str Tap	2/0 AWG

Configuration

Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Crimps Required	1
Connector Type	T-Connector

Dimensions

Package Height	0.000 in
Dimension - Height mm	35.1 mm
Dimension - Height inch	1.38 in
Dimension - B Length fraction	1-3/8 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	108 mm
Dimension - B Length inch	2.00 in
Dimension - Length BB inch	1.38 in
Dimension - Length Overall inch	4.25 in

Force Related

Installation Torque Recommended in-lb	240 LBS/in
---------------------------------------	------------

General

Plated	Y
Die Index	13
One Wrench Installation	Y
UPC	781810081969
Material	Copper Alloy
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810081969
UPC 14 Digit GTIN	00781810081969

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)