


NA122N, Substation - Copper Terminal

By Burndy
Catalog # [NA122N](#)

Substation Connectors



Features

- Type NA for Copper Tube to Pad
- High copper alloy terminal for joining copper tube to a flat pad
- Letter N on end of the catalog number indicates pad drilled to NEMA standards
- One-wrench installation

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Number Of Conductors	1
Conductor - Connection Combination	Tube to Flat
Conductor Type	• CU Tube Std-Size • CU Tube EH-Size
Conductor - Copper Tube Std Size Range	3/8 IPS
Conductor - Copper Tube Std Size	3/8 IPS
Conductor - Copper Tube EH Size Range	3/8 IPS
Conductor - Copper Tube EH Size	3/8 IPS

Configuration

Physical Attribute - Pad Configuration	2 holes
Physical Attribute - Pad Alignment	Offset

Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.50 in
Package Height	0.000 in
Dimension - Height mm	38.1 mm
Dimension - Hole Size fraction	9/16
Dimension - Height inch	1.50 in
Dimension - Height fraction	1-1/2 in
Package Weight	0.000 lb.
Dimension - Width mm	54 mm
Dimension - Width inch	2.13 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	95 mm
Dimension - B Length inch	1.38 in
Dimension - Length Overall inch	3.75 in

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Clamping Element Design	Body and Cap
UPC	781810065990
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810065990
UPC 14 Digit GTIN	00781810065990

Logistics

Minimum Pack Quantity	18
Pallet Quantity	1680
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)