



NA184N, Substation - Copper Terminal, 2" Cu Pipe, 4-Hole NEMA

By Burndy
Catalog # [NA184N](#)

Copper Bolted Terminal, Tube to Flat, 2" Cu Pipe, 4 Pad Holes ,
230 kV

Features

- Type NA for Copper Tube to Pad
- High copper alloy terminal for joining copper tube to a flat pad
- Letter N on end of the catalog number indicates pad drilled to NEMA standards
- One-wrench installation

Application

Substation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor


Number Of Conductors	1
Conductor - Connection Combination	Tube to Flat
Conductor Type	• CU Tube Std-Size • CU Tube EH-Size
Conductor - Copper Tube Std Size Range	2 IPS
Conductor - Copper Tube Std Size	2 IPS
Conductor - Copper Tube EH Size Range	2 IPS
Conductor - Copper Tube EH Size	2 IPS

Configuration

Physical Attribute - Pad Configuration	3.13 x 3.13 - 4 holes
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Number of Holes	4



A Hubbell brand



Connector Type	Terminal
----------------	----------

Dimensions

Dimension - Pad Width inch	3.13 in
Package Height	0.000 in
Dimension - Height mm	79.5 mm
Dimension - Hole Size fraction	9/16
Dimension - Height inch	3.13 in
Dimension - Height fraction	3-1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	151 mm
Dimension - Width mm	118 mm
Dimension - Width inch	4.63 in
Dimension - B Length inch	2.69 in
Dimension - D inch	3.13 in
Dimension - N inch	0.63 in
Dimension - Length Overall inch	5.94 in

General

Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Plated	N
Clamping Element Design	Body and Cap
UPC	781810002490
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810002490
UPC 14 Digit GTIN	00781810002490

Logistics

Minimum Pack Quantity	2
Pallet Quantity	144
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)