




NA20ACG2, Substation - Aluminum Bolted Terminal

By Burndy
Catalog # [NA20ACG2](#)

Substation Connectors

Features

- Type NA-A Aluminum Terminals for Tube to Pad
- Properly proportioned to minimize conductor corrosion due to galvanic action
- When properly used, this item does not require use of bimetallic plates, contact Burndy Technical Support for recommendations
- One-wrench installation

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Tube Std Size Range	3 IPS
Conductor - AL Tube Std Size	3 IPS
Conductor Type	• AL Tube Std-Size • CU Tube Std-Size
Conductor - Copper Tube Std Size Range	3 IPS IPS
Conductor - Copper Tube Std Size	3 IPS IPS

Configuration

Physical Attribute - Pad Orientation	Straight
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3.50 in
Package Height	0.000 in
Dimension - Height mm	129.3 mm
Dimension - Height inch	5.09 in
Package Weight	0.000 lb.
Dimension - Width mm	140 mm
Dimension - Width inch	5.50 in
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	230 mm
Dimension - B Length inch	5.00 in
Dimension - D inch	3.50 in
Dimension - N inch	0.88 in
Dimension - Length Overall inch	9.06 in

General

Plated	N
Material - Hardware	Aluminum
UPC	781810484234
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810484234
UPC 14 Digit GTIN	00781810484234

Logistics

Minimum Pack Quantity	3
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)