




Substation - Aluminum Bolted Terminal

By Burndy
Catalog # [NAC20A34N](#)

Substation Connectors



Application

Substation

Specifications

Certification - ETL No
Standards - RoHS Compliance EX
Status

Conductor

Conductor - AL Tube Std Size Range 3 IPS
Conductor - AL Tube Std Size Number Of Conductors 1
Conductor - Connection Combination Tube to Flat
Conductor - Copper Tube Std Size Range 3 IPS IPS
Conductor - Copper Tube Std Size 3 IPS IPS

Configuration

Physical Attribute - Pad Orientation Straight
Physical Attribute - Pad Configuration 3 x 3.25 - 4 holes
Physical Attribute - Pad Alignment Centered
Physical Attribute - Number of Holes 4
Connector Type Terminal

Dimensions

Dimension - Pad Size inch 3 x 3.25

Dimension - Pad Width inch 3.00 in
Dimension - Height mm 137.7 mm
Dimension - Hole Size fraction 9/16
Dimension - Height inch 5.42 in
Dimension - Width mm 143 mm
Dimension - Width inch 5.62 in
Dimension - F Width Center to Center inch 1.75 in
Dimension - L Length Overall mm 240 mm
Dimension - B Length inch 5.00 in
Dimension - D inch 3.25 in
Dimension - N inch 0.62 in
Dimension - Hole Size inch 0.56 in
Dimension - Length Overall inch 9.44 in

Force Related

Installation Torque Recommended in-lb 480 LBS/in

General

Plated N
Material - Hardware Aluminum
One Wrench Installation Y
Clamping Element Design Body and Cap
UPC 781810263143
Material Aluminum Alloy
Plating Type Unplated
UPC 12 Digit 781810263143
UPC 14 Digit GTIN 00781810263143

Product Assets

[Catalog \[English\]](#)