




Substation - Copper Terminal

By Burndy

Catalog # [NAH3434N90](#)

Substation Connectors



Application

Substation

Physical Attribute - Number of Holes

4

Connector Type

Terminal

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	1/0 AWG 2/0 AWG 3/0 AWG 4/0 AWG
Number Of Conductors	1
Conductor - Connection Combination	Cable to Flat
Conductor - Copper Solid Size Range	1/0 AWG-4/0 AWG
Conductor Type	- CU C Str-Size - CU C Solid-Size
Conductor - Copper Str Size Range	1/0 -500 kcmil
Conductor - Copper Str Size	1/0 2/0 AWG 3/0 AWG 4/0 AWG 250 kcmil 300 kcmil 350 kcmil 400 kcmil 450 kcmil 500 kcmil

Configuration

Physical Attribute - Pad Orientation	90 Degree
Physical Attribute - Pad Configuration	3 x 3 - 4 holes
Physical Attribute - Pad Alignment	Offset

Dimensions

Dimension - Pad Size inch	3 x 3
Dimension - Pad Width inch	3.00 in
Package Height	0.000 in
Dimension - Height mm	136.7 mm
Dimension - Hole Size fraction	9/16
Dimension - Height inch	5.38 in
Package Weight	0.000 lb.
Dimension - Width mm	65 mm
Dimension - Width inch	2.56 in
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	129 mm
Dimension - B Length inch	2.62 in
Dimension - D inch	3.00 in
Dimension - N inch	0.62 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	5.06 in

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Clamping Element Design	Body and Cap
UPC	781810171820
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810171820
UPC 14 Digit GTIN	00781810171820

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)

