



Substation - Connector

By Burndy
Catalog # [NBC22A44N](#)

Substation Connectors



Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Tube Std Size Range	4 IPS
Conductor - AL Tube Std Size	4 IPS
Conductor - Connection	Tube to Flat
Combination	
Conductor Type	AL Tube Std-Size

Configuration

Physical Attribute - Pad Orientation	Straight
Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Pad Configuration	4 x 4.25 - 4 holes
Physical Attribute - Pad Alignment	Centered
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Holes	4
Connector Type	T-Connector

Dimensions

Dimension - Pin Diameter inch	4.50 in
Dimension - Pin Diameter fraction	4-1/2 in

Dimension - Pad Size inch	4 x 4.25
Dimension - Pad Width inch	4.00 in
Dimension - Height mm	139.7 mm
Dimension - Hole Size fraction	9/16
Dimension - Height inch	5.50 in
Dimension - Height fraction	5-1/2 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - L Length Overall mm	289 mm
Dimension - B Length inch	6.00 in
Dimension - D inch	4.25 in
Dimension - N inch	1.12 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	11.37 in

Force Related

Installation Torque Recommended in-lb	480 LBS/in
---------------------------------------	------------

General

Plated	N
Trade Name	BARTAP™
Material - Hardware	Aluminum
One Wrench Installation	Y
UPC	781810104163
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810104163
UPC 14 Digit GTIN	00781810104163

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)