




Substation - Connector

By Burndy
Catalog # [NDR65544T12TN](#)

Copper Stud Connectors

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	2 4/0
Number Of Conductors	1
Conductor - Connection Combination	- Stud to Cable - Stud to Tube - Stud to Bar
Conductor - Copper Solid Size Range	2-4/0
Conductor - Copper Tube DEH Size Range	3/8 IPS-3/4 IPS
Conductor Type	- CU C Str-Size - CU Tube Std-Size - CU C Solid-Size
Conductor - Copper Tube DEH Size	3/8 IPS 3/4 IPS
Conductor - Copper Str Size Range	2-1000
Conductor - Copper Str Size	2 1000
Conductor - Copper Tube Std Size Range	3/8 IPS-3/4 IPS
Conductor - Copper Tube Std Size	3/8 IPS 3/4 IPS
Conductor - Copper Tube EH Size Range	3/8 IPS-3/4 IPS
Conductor - Copper Tube EH Size	3/8 IPS 3/4 IPS

Configuration

Connector Type	Stud Connector
----------------	----------------

Dimensions

Dimension - Pin Diameter inch	1.125 in
Dimension - Pin Diameter fraction	1-1/8 in
Package Height	0.000 in
Dimension - Height mm	71.6 mm
Dimension - Height inch	2.82 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - AA Pad Orientation	- In-line 90°
Package Width	0.000 in
Dimension - L Length Overall mm	118 mm
Dimension - B Length inch	1.53 in
Dimension - Threads per inch	12
Dimension - Length Overall inch	4.66 in

General

Plated	Y
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810100127
Material	Copper Alloy
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810100127
UPC 14 Digit GTIN	00781810100127

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)