



NHNT2229, Substation Copper T Connector, 90 Degrees

By Burndy
Catalog # [NHNT2229](#)

Substation Connectors

Features

- High copper alloy reversible T-Connector for joining a wide range of run pipe and tap cables
- Connector is designed for one-wrench installation

Application


Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Connection Combination	Tube to Cable
Conductor - Copper Solid Tap Range	5 AWG-4/0 AWG
Conductor - Copper Solid Tap	• 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor Type	• CU Tube Std-Run • CU C Str-Run • CU C Solid-Run • CU C Str-Tap • CU C Solid-Tap
Conductor - Copper Str Tap Range	6 AWG-250 kcmil
Conductor - Copper Str Tap	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0



- 2/0 AWG
- 3/0 AWG
- 4/0 AWG
- 250 kcmil

Conductor - Copper Tube Std Run Range	4 IPS
Conductor - Copper Tube Std Run	4 IPS

Configuration

Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Number of Run Conductors	1
Connector Type	T-Connector

Dimensions

Dimension - Height mm	108.2 mm
Dimension - Height inch	4.26 in
Dimension - Width mm	64 mm
Dimension - Width inch	2.50 in
Dimension - L Length Overall mm	264 mm
Dimension - B Length inch	3.25 in
Dimension - Length BB inch	2.63 in
Dimension - Length Overall inch	10.38 in

Force Related

Installation Torque Recommended in-lb	480 LBS/in
---------------------------------------	------------

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
UPC	781810219676
Type	Tube to Cable Couplers
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810219676
UPC 14 Digit GTIN	00781810219676

Logistics

Minimum Pack Quantity	1
-----------------------	---

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)



A Hubbell brand