



QA442NTN, 2-Hole, Heavy Duty Copper Terminal

By Burndy
Catalog # [QA442NTN](#)



850-1000 kcmil, 2-Hole, 1/2" Stud, 1.75" Spacing, Single Clamping Element, Compact Design, Tin Plated

Features

- QIKLUG™ Terminals feature compact size, high copper alloy terminal for joining cables to equipment pads or bars
- Each element accommodates a wide range of cable
- One-wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Navy Size Range	1000 (127) Navy
Conductor - Copper Str Navy Size	1000 (127) Navy
Conductor Type	• CU C Str-Size • CU C Str Navy-Size
Conductor - Copper Str Size Range	900 kcmil-1000 kcmil
Conductor - Copper Str Size	• 900 kcmil • 1000 kcmil

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	2
Connector Type	Single Clamp

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Dimension - Pad Width inch	1.88 in
Package Height	0.000 in
Dimension - Height mm	63.5 mm
Dimension - Height inch	2.50 in
Dimension - Height fraction	2.5 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	125 mm
Dimension - D inch	3.00 in
Dimension - N inch	0.62 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	4.94 in
Dimension - Stud Size inch	1/2

Force Related

Installation Torque	500 LBS/in
Recommended in-lb	

General

Physical Attribute - Screw Type Plated	Hexagonal Bolt Y
Trade Name	QIKLUG™
UPC	781810247389
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810247389
UPC 14 Digit GTIN	00781810247389

Logistics

Minimum Pack Quantity	6
-----------------------	---

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)