



QA4C2BTN, 2-Hole, Heavy Duty Copper Terminal

By Burndy
Catalog # [QA4C2BTN](#)



8-4 AWG Str, 2-Hole, 1/4" Stud, .625" Spacing, Single Clamping Element, Compact Design, Tin Plated

Features

- QIKLUG™ Terminals feature compact size, high copper alloy terminal for joining cables to equipment pads or bars
- Each element accommodates a wide range of cable
- One-wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Size	#8-#4 AWG
Conductor - Copper Str Navy Size Range	23 (7) Navy-40 (19) Navy
Conductor - Copper Str Navy Size	• 23 (7) Navy • 30 (19) Navy • 40 (19) Navy
Conductor Type	• CU C Str-Size • CU C Str Navy-Size
Conductor - Copper Str Size Range	8 AWG-4 AWG
Conductor - Copper Str Size	• 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	2
Connector Type	Single Clamp

Dimensions

Dimension - Pad Width inch	0.62 in
Package Height	0.000 in
Dimension - Height mm	19.1 mm
Dimension - Height inch	0.75 in
Dimension - Height fraction	3/4 in
Package Weight	0.000 lb.
Dimension - Width mm	16 mm
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	51 mm
Weight	0.1 lb.
Dimension - D inch	1.19 in
Dimension - N inch	0.31 in
Dimension - Hole Size mm	7 mm
Dimension - Hole Size inch	0.28 in
Dimension - Length Overall inch	2.00 in
Dimension - Stud Size inch	1/4

Force Related

Installation Torque Recommended in-lb	110 LBS/in
---------------------------------------	------------

General

Physical Attribute - Screw Type Plated	Hexagonal Bolt Y
Trade Name	QIKLUG™
UPC	781810145685
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Tin - Electro Plated
UPC 14 Digit GTIN	00781810145685

Logistics

Minimum Pack Quantity	25
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)