



QA8C2B, 2-Hole, Heavy Duty Copper Terminal

By Burndy
Catalog # [QA8C2B](#)

14 AWG Sol-8 AWG Str, 2-Hole, #10 Stud, .625" Spacing, Single Clamping Element, Compact Design



Features

- QIKLUG™ Terminals feature compact size, high copper alloy terminal for joining cables to equipment pads or bars
- Each element accommodates a wide range of cable
- One-wrench installation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 14 AWG • 12 AWG • 10 AWG • 9 AWG • 8 AWG
Conductor Size	14-8 AWG
Conductor - Copper Str Navy Size Range	4 (1) Navy-14 (140) Navy
Conductor - Copper Str Navy Size	• 4 (1) Navy • 4 (7) Navy • 4 (19) Navy • 4 (41) Navy • 6 (7) Navy • 6 (19) Navy • 9 (7) Navy • 9 (37) Navy • 14 (7) Navy • 14 (140) Navy
Conductor - Copper Solid Size	• 14 AWG • 13 AWG • 12 AWG • 11 AWG • 10 AWG • 9 AWG • 8 AWG

Conductor - Copper Solid Size Range 14 AWG-8 AWG

Conductor Type

- CU C Str-Size
- CU C Str Navy-Size

Conductor - Copper Str Size Range 14 AWG-8 AWG

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	2
Connector Type	Single Clamp

Dimensions

Dimension - Pad Width inch	0.56 in
Package Height	0.000 in
Dimension - Height mm	17.5 mm
Dimension - Hole Size fraction	7/32
Dimension - Height inch	0.69 in
Dimension - Height fraction	11/16
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	.625 in
Package Width	0.000 in
Dimension - L Length Overall mm	51 mm
Weight	0.1 lb.
Dimension - Hole Size mm	6 mm
Dimension - Hole Size inch	0.22 in
Dimension - Stud Size inch	#10
Dimension - Bolt Size fraction	#1
Dimension - Width mm	14 mm
Dimension - Width inch	9/16 in
Dimension - D inch	1.19 in
Dimension - N inch	0.31 in
Dimension - Length Overall inch	2 in

Force Related

Installation Torque Recommended in-lb	75 LBS/in
---------------------------------------	-----------

General

Trade Name	QIKLUG™
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
UPC	781810313701
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810313701

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)



A Hubbell brand