



QPX2C2CY, Mech. Parallel Clamp, Cu/Al, Mult. Configurations

By Burndy
Catalog # QPX2C2CY



Run #6-#2 AWG, Tap #6-#2 AWG, Capable of Tee, Cross, Parallel, Butt and Tap Configurations, Tin Plated

Features

- VERSITAP™ Type QPX-Y Parallel Clamps for copper or aluminum are capable of Tee, Cross, Parallel, Butt and Tap configurations
- Range-taking, only 10 connectors are required to accommodate conductor sizes from #6 Stranded to 1000 kcmil
- Edges are rounded for easy taping

Application

For Use With Copper Or Aluminum Cable

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	6 AWG-2 AWG
Conductor - AL Str Run	• 6 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - AL Str Tap Range	6 AWG-2 AWG
Conductor - AL Str Tap	• 6 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - Copper Str Run Range	6 AWG-2 AWG
Conductor - Copper Str Run	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor Type	• AL C Str-Run

- CU C Str-Run
 - AL C Str-Tap
 - CU C Str-Tap
- 6 AWG-2 AWG

Conductor - Copper Str Tap Range

Conductor - Copper Str Tap

- 6 AWG
- 5 AWG
- 4 AWG
- 3 AWG
- 2 AWG

Configuration

Physical Attribute - Number of Screws	2
Connector Type	Universal Clamp

Dimensions

Package Height	0.000 in
Dimension - Height mm	41.4 mm
Dimension - Height inch	1.59
Dimension - Height fraction	1-5/8 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	38 mm
Dimension - Width fraction	1-5/8 in
Dimension - B Length fraction	1-1/2 in
Dimension - Width mm	41 mm
Dimension - Width inch	1.61
Dimension - B Length inch	1.52 in
Dimension - Length Overall inch	1.50 in

Force Related

Installation Torque Recommended in-lb	150 LBS/in
---------------------------------------	------------

General

Trade Name	VERSITAP™
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type Plated	Hexagonal Bolt Y
Sub Brand	VERSITAP
UPC	781810341803

Type	QPX-Y, Universal	Minimum Pack Quantity	24
Material	Copper		
Plating Type	Tin		
UPC 12 Digit	781810341803		
UPC 14 Digit GTIN	00781810341803		

Logistics

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)



A Hubbell brand