



Substation - Aluminum Bolted T Connector

By Burndy
Catalog # [NNT18A15A](#)

Substation Connectors



Features

- Type NNT Aluminum T-Connectors for Aluminum and Copper Tube to Tube
- Properly proportioned to permit use on copper-aluminum conductor combinations
- Captured hex head bolts permit one-wrench installation

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Tube Std Run Range	2 IPS
Conductor - AL Tube Std Run	2 IPS
Conductor - Connection Combination	Tube to Tube
Conductor - AL Tube Std Tap Range	1 IPS
Conductor - AL Tube Std Tap	1 IPS
Conductor Type	• AL Tube Std-Run • AL Tube Std-Tap

Configuration

Physical Attribute - Pad Orientation	90 Degree
Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Number of Run Conductors	1
Connector Type	T-Connector

Dimensions

Package Height	0.000 in
Dimension - Height mm	111.3 mm
Dimension - Height inch	4.38 in
Package Weight	0.000 lb.
Dimension - Width mm	78 mm
Dimension - Width inch	3.06 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	202 mm
Dimension - B Length inch	4.00 in
Dimension - Length BB inch	3.50 in
Dimension - Length Overall inch	7.94 in

Force Related

Installation Torque	300 LBS/in
Recommended in-lb	

General

Plated	N
Material - Hardware	Aluminum
One Wrench Installation	Y
UPC	781810119471
Type	Bolted Tees
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810119471
UPC 14 Digit GTIN	00781810119471

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)