



QPX442C, Mech. Parallel Clamp for Cu, Mult. Configurations

By Burndy
Catalog # [QPX442C](#)

Run 500-1000 kcmil, Tap #6-#2 AWG, Capable of Tee, Cross, Parallel, Butt and Tap Configurations

Features

- VERSITAP™ Type QPX Parallel Clamps for copper are capable of Tee, Cross, Parallel, Butt and Tap configurations
- Range-taking, only 10 connectors are required to accommodate conductor sizes from #6 Stranded to 1000 kcmil
- Edges are rounded for easy taping

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Run Range	500 kcmil-1000 kcmil
Conductor - Copper Str Run	• 500 kcmil • 550 kcmil • 600 kcmil • 700 kcmil • 750 kcmil • 800 kcmil • 850 kcmil • 900 kcmil • 1000 kcmil
Conductor Type	• CU C Str-Run • CU C Str-Tap
Conductor - Copper Str Tap Range	6 AWG-2 AWG
Conductor - Copper Str Tap	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG

Configuration



Connector Type Universal Clamp

Current

Rating - Minimum Voltage 600

Dimensions

Package Height	0.000 in
Dimension - Height mm	66.8 mm
Dimension - Height inch	2.69
Dimension - Height fraction	2-11/16
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	35 mm
Dimension - Width fraction	2-1/4 in
Dimension - Width mm	57 mm
Dimension - Width inch	2.22
Dimension - Length Overall inch	1.38 in

Force Related

Installation Torque 180 LBS/in
Recommended in-lb

General

Trade Name	VERSITAP™
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
UPC	781810344750
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810344750
UPC 14 Digit GTIN	00781810344750

Logistics

Minimum Pack Quantity	12
Pallet Quantity	1
Carton Quantity	1

Operational

Temperature Rating 194



A Hubbell brand