

Substation - Aluminum Bolted T Connector

By Burndy
Catalog # [NNT20A20A](#)

Substation Connectors



Features

- Type NNT Aluminum T-Connectors for Aluminum and Copper Tube to Tube
- Properly proportioned to permit use on copper-aluminum conductor combinations
- Captured hex head bolts permit one-wrench installation

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Tube Std Run Range	3 IPS
Conductor - AL Tube Std Run	3 IPS
Conductor - Connection Combination	Tube to Tube
Conductor - AL Tube Std Tap Range	3 IPS
Conductor - AL Tube Std Tap	3 IPS
Conductor Type	• AL Tube Std-Run • AL Tube Std-Tap

Configuration

Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Number of Run Conductors	1

Connector Type	T-Connector
----------------	-------------

Dimensions

Dimension - Height mm	138.2 mm
Dimension - Height inch	5.44 in
Dimension - Height fraction	5
Dimension - B Length fraction	5 in
Dimension - Width mm	143 mm
Dimension - Width inch	5.63 in
Dimension - L Length Overall mm	278 mm
Dimension - B Length inch	5.00 in
Dimension - Length BB inch	5.00 in
Dimension - Length Overall inch	10.94 in

Force Related

Installation Torque Recommended in-lb	480 LBS/in
---------------------------------------	------------

General

Plated	N
Material - Hardware	Aluminum
One Wrench Installation	Y
UPC	781810092149
Type	Bolted Tees
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810092149
UPC 14 Digit GTIN	00781810092149

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)