

QQA26, Twin Clamping, 1-Hole, Heavy Duty Copper Terminal

By Burndy
Catalog # [QQA26](#)

1/0-2/0 AWG Cu Str, 1-Hole, 3/8" Stud, 2 Clamping Elements, 1-Wrench Installation



Features

- QIKLUG™ Terminals feature compact size, high copper alloy terminal for joining cables to equipment pads or bars
- Each element accommodates a wide range of cable
- One-wrench installation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	EX
Status	
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 1/0 • 2/0 AWG
Conductor Size	1/0-2/0 AWG
Conductor - Copper Str Navy Size Range	100 (61) Navy-125 (61) Navy
Conductor - Copper Str Navy Size	• 100 (61) Navy • 125 (61) Navy
Conductor Type	• CU C Str-Size • CU C Str Navy-Size
Conductor - Copper Str Size Range	1/0 -2/0 AWG

Configuration

Physical Attribute - Number of Screws	2
Physical Attribute - Number of Holes	1
Connector Type	Duel Clamp

Dimensions

Dimension - Pad Width inch	0.81 in
Package Height	0.000 in
Dimension - Height mm	28.7 mm
Dimension - Height inch	1.13 in
Dimension - Height fraction	1.125 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	81 mm
Dimension - Hole Size mm	10 mm
Dimension - Hole Size inch	0.41 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	0.94 in
Dimension - N inch	0.44 in
Dimension - Length Overall inch	3.19 in

Force Related

Installation Torque	180 LBS/in
Recommended in-lb	

General

Trade Name	QIKLUG™
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
UPC	781810325704
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810325704

Logistics

Minimum Pack Quantity	7
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)