



QQA342N, Twin Clamping, 2-Hole, Heavy Duty Copper Terminal

By Burndy
Catalog # [QQA342N](#)



400-500 kcmil Cu, 2-Hole, 1/2" Stud, 1.75" Spacing, 2 Clamping Elements

Features

- QIKLUG™ Terminals feature compact size, high copper alloy terminal for joining cables to equipment pads or bars
- Each element accommodates a wide range of cable
- One-wrench installation

Application

For Copper Cable

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 400 kcmil • 450 kcmil • 500 kcmil
Conductor Size	400-500 kcmil
Conductor - Copper Str Navy Size Range	400 (127) Navy-500 (127) Navy
Conductor - Copper Str Navy Size	• 400 (127) Navy • 500 (127) Navy
Conductor Type	• CU C Str-Size • CU C Str Navy-Size
Conductor - Copper Str Size Range	400 kcmil-500 kcmil

Configuration

Physical Attribute - Number of Screws	2
Physical Attribute - Number of Holes	2
Connector Type	Dual Clamp

Dimensions

Dimension - Pad Width inch	1.38 in
Package Height	0.000 in
Dimension - Height mm	50.8 mm
Dimension - Height inch	2.00 in
Dimension - Height fraction	2 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	162 mm
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.13 in
Dimension - N inch	0.63 in
Dimension - Length Overall inch	6.38 in

Force Related

Installation Torque	375 LBS/in
Recommended in-lb	

General

Trade Name	QIKLUG™
Physical Attribute - Screw Type Plated	Hexagonal Bolt N
Sub Brand	QIKLUG
UPC	781810326107
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810326107

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)



A Hubbell brand