




# QQA344N, Twin Clamping, 4-Hole, Heavy Duty Copper Terminal

By Burndy  
Catalog # [QQA344N](#)



400-500 kcmil Cu, 4-Hole, 1/2" Stud, 1.75" Spacing, 2 Clamping Elements

### Features

- QIKLUG™ Terminals feature compact size, high copper alloy terminal for joining cables to equipment pads or bars
- Each element accommodates a wide range of cable
- One-wrench installation

### Specifications

|                                    |              |
|------------------------------------|--------------|
| Certification - UL Recognized      | No           |
| Certification - cULus              | No           |
| Industry Standard(s)               | UL 486A-486B |
| Certification - ETL                | No           |
| Standards - Industry Standards Met | UL 486A-486B |
| Standards - RoHS Compliance        | EX           |
| Status                             |              |
| UL Listed                          | Yes          |
| Certification - CSA Approved       | No           |

### Conductor

|                                   |                                                                                                     |
|-----------------------------------|-----------------------------------------------------------------------------------------------------|
| Conductor - Copper Str Size       | <ul style="list-style-type: none"><li>• 400 kcmil</li><li>• 450 kcmil</li><li>• 500 kcmil</li></ul> |
| Conductor Size                    | 400-500 kcmil                                                                                       |
| Conductor Type                    | <ul style="list-style-type: none"><li>• CU C Str-Size</li><li>• CU C Str Navy-Size</li></ul>        |
| Conductor - Copper Str Size Range | 400 kcmil-500 kcmil                                                                                 |

### Configuration

|                                       |            |
|---------------------------------------|------------|
| Physical Attribute - Number of Screws | 2          |
| Physical Attribute - Number of Holes  | 4          |
| Connector Type                        | Duel Clamp |

### Current

|                          |     |
|--------------------------|-----|
| Rating - Minimum Voltage | 600 |
|--------------------------|-----|

### Dimensions

|                            |         |
|----------------------------|---------|
| Dimension - Pad Width inch | 3.00 in |
|----------------------------|---------|

|                                           |            |
|-------------------------------------------|------------|
| Package Height                            | 0.000 in   |
| Dimension - Height mm                     | 49.3 mm    |
| Dimension - Height inch                   | 1.94 in    |
| Dimension - Height fraction               | 1-15/16 in |
| Package Weight                            | 0.000 lb.  |
| Package Length                            | 0.000 in   |
| Dimension - F Width Center to Center inch | 1.75 in    |
| Package Width                             | 0.000 in   |
| Dimension - L Length Overall mm           | 165 mm     |
| Dimension - Hole Size mm                  | 14 mm      |
| Dimension - Hole Size inch                | 0.56 in    |
| Dimension - Bolt Size fraction            | 1/2        |
| Dimension - D inch                        | 3.06 in    |
| Dimension - N inch                        | 0.62 in    |
| Dimension - Length Overall inch           | 6.50 in    |

### General

|                   |                         |
|-------------------|-------------------------|
| Trade Name        | QIKLUG™                 |
| Plated            | N                       |
| UPC               | 781810006023            |
| Type              | Bolted Lugs & Terminals |
| Material          | Copper                  |
| Plating Type      | Unplated                |
| UPC 12 Digit      | 781810006023            |
| UPC 14 Digit GTIN | 00781810006023          |

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
| Pallet Quantity       | 1 |
| Carton Quantity       | 1 |

### Operational

|                    |     |
|--------------------|-----|
| Temperature Rating | 194 |
|--------------------|-----|

### Product Assets

[Catalog \[English\]](#)  
[Installation Manual \[English\]](#)