



Substation - Copper Coupler - Straight

By Burndy
Catalog # [NS1313](#)

Cast Cu Alloy Bolted Coupler,1/2" IPS, Silicon Bronze H/W



Features

- Type NS Copper Bolted Coupler, for Copper Straight Tube to Tube
- High copper alloy coupler for joining equal sizes of tube end to end
- Slots between bolts provide independent high pressure areas of contact
- One-wrench installation

Application

Substation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Connection Combination	Tube to Tube
Conductor Type	CU Tube Std-Size
Conductor - Copper Tube Std Size Range	1/2 IPS
Conductor - Copper Tube Std Size	1/2 IPS

Configuration

Physical Attribute - Pad Orientation	Straight
Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Number of Run Conductors	1
Connector Type	Couplers

Dimensions

Package Height	0.000 in
Dimension - Height mm	42.9 mm
Dimension - Height inch	1.69 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	83 mm
Dimension - Width mm	57 mm
Dimension - Width inch	2.25 in
Dimension - B Length inch	1.63 in
Dimension - Length BB inch	1.63 in
Dimension - Length Overall inch	3.25 in

Force Related

Installation Torque	240 LBS/in
Recommended in-lb	

General

Material - Hardware	Silicon Bronze
One Wrench Installation	Y
Plated	N
UPC	781810002513
Type	Tube to Tube Couplers
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810002513
UPC 14 Digit GTIN	00781810002513

Logistics

Minimum Pack Quantity	10
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)