



QQA442N, Twin Clamping, 2-Hole, Heavy Duty Copper Terminal

By Burndy
Catalog # [QQA442N](#)



850-1000 kcmil, 2-Hole, 1/2" Stud, 1.75" Spacing, 2 Clamping Elements, 1-Wrench Installation

Features

- QIKLUG™ Terminals feature compact size, high copper alloy terminal for joining cables to equipment pads or bars
- Each element accommodates a wide range of cable
- One-wrench installation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 900 kcmil • 1000 kcmil
Conductor Size	850-1000 kcmil
Conductor - Copper Str Navy Size Range	1000 (127) Navy
Conductor - Copper Str Navy Size	1000 (127) Navy
Conductor Type	• CU C Str-Size • CU C Str Navy-Size
Conductor - Copper Str Size Range	900 kcmil-1000 kcmil

Configuration

Physical Attribute - Number of Screws	2
Physical Attribute - Number of Holes	2
Connector Type	Duel Clamp

Dimensions

Dimension - Pad Width inch	1.88 in
----------------------------	---------

Package Height	0.000 in
Dimension - Height mm	63.5 mm
Dimension - Height inch	2.50 in
Dimension - Height fraction	2.5 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	179 mm
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.00 in
Dimension - N inch	0.63 in
Dimension - Length Overall inch	7.06 in

Force Related

Installation Torque	500 LBS/in
Recommended in-lb	

General

Trade Name	QIKLUG™
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
UPC	781810006122
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810006122

Logistics

Minimum Pack Quantity	2
Pallet Quantity	432
Carton Quantity	3

Product Assets

[Catalog \[English\]](#)