

Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [S2GBPA486A](#)



Substation Connectors

Features

- Streamlined rigid spacer for large range of cables
- 1 bolt per clamping module
- EHV Rated: Self-Shielding up to 550kV

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 2300 kcmil • 2500 kcmil
Conductor - AL Str Size Range	2300 kcmil-2500 kcmil
Conductor - ACSR Str Size	• 2156 (84/19) Bluebird kcmil • 2167 (72/7) Kiwi kcmil
Conductor - ACSR Str Size Range	2156 (84/19) Bluebird kcmil-2167 (72/7) Kiwi kcmil

Configuration

Physical Attribute - Pad Orientation	90 Degree
Connector Type	Spacer

Dimensions

Dimension - G inch	5.59 in
Dimension - Pad Width inch	4.00 in
Dimension - Height mm	181.6 mm
Dimension - Height inch	7.15 in
Dimension - Width mm	102 mm
Dimension - Width inch	4.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - L Length Overall mm	518 mm
Dimension - B Length inch	4.00 in
Dimension - D inch	4.50 in
Dimension - N inch	1.12 in
Dimension - Length Overall inch	20.38 in

General

Plated	N
UPC	781810283325
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810283325
UPC 14 Digit GTIN	00781810283325

Logistics

Minimum Pack Quantity	2
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)