

Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [S2R484ACG3](#)



Rigid 13 IN Spacer, 2303 kcmil AAC, 500kV

Features

- Rigid aluminum spacer
- 2 bolt installation with captured hex head bolts permit one-wrench installation

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Number Of Conductors	2
Conductor - Connection Combination	Cable Spacer
Conductor - AL Str Size Range	2303 kcmil

Configuration

Connector Type	Spacer
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Height mm	79.2 mm
Dimension - Height inch	3.12 in

Package Weight	0.000 lb.
Dimension - Width mm	76 mm
Dimension - Width inch	3.00 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	397 mm
Dimension - B Length inch	3.00 in
Dimension - Length Overall inch	15.62 in

Force Related

Installation Torque Recommended in-lb	660 in-lb
---------------------------------------	-----------

General

Plated	N
One Wrench Installation	Y
Clamping Element Design	2 Piece Design
UPC	781810424056
Material	Aluminum Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810424056
UPC 14 Digit GTIN	00781810424056

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)