

Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [S2R496A15S7HQ](#)



Rigid 15 IN Spacer, 735kV

Features

- Rigid aluminum spacer
- 2 bolt installation with captured hex head bolts permit one-wrench installation

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Number Of Conductors	2
Conductor - Connection Combination	Cable Spacer

Configuration

Connector Type	Spacer
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Length	18.3 in
Dimension - Height inch	4.10 in
Package Weight	0.000 lb.
Dimension - Width mm	76 mm
Dimension - Width inch	3.00 in
Package Length	0.000 in

Package Width	0.000 in
Dimension - L Length Overall mm	465 mm
Dimension - B Length inch	3.00 in
Height	3 in
Width	4.1 in
Dimension - Diameter Min Size inch	2.28 in
Dimension - Diameter Max Size inch	2.50 in
Dimension - Length Overall inch	18.30 in
Dimensions	18.3 in x 4.1 in x 3 in

Force Related

Installation Torque Recommended in-lb	660 in-lb
---------------------------------------	-----------

General

Plated	N
One Wrench Installation	Y
UPC	781810480120
Material	Aluminum Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810480120
UPC 14 Digit GTIN	00781810480120

Logistics

Minimum Pack Quantity	2
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)