



SNM14, Nylon Splice For 16 - 14 AWG

By Burndy
Catalog # [SNM14](#)

Nylon Splice For 16 - 14 AWG



Features

- High Quality Nylon Butt Splice
- Tin Plated, Seamless Tubing with Integral Barrel/Insulation Grip providing maximum tensile strength
- Smooth Funnel Entry for easy wire insertion

Application

The type SNM INSULINK is a high quality nylon insulated butt splice designed to meet military MS25181, class 1 requirements.

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	UL486
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Size	• 16 AWG • 14 AWG
Conductor Size	16 - 14 AWG
Conductor - Copper Str Size Range	16 - 14 AWG

Configuration

Connector Type	Seamless Butt Splice
----------------	----------------------

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - Outside Diameter	0.15 in
Dimension - L Length Overall	39 mm
Dimension - Strip Length inch	7/32 in
Cable Insulation Diameter	0.150 in
Maximum	
Dimension - Length Overall	1.53 in
Dimension - Diameter Max Size	0.15 in
inch	

General

Insulation Type	Nylon
Trade Name	INSULINK™
Insulation	Y
Sub Brand	INSULINK
Color Code	Blue
Plated	Y
Type	SNM
UPC 12 Digit	781810736555
UPC 14 Digit GTIN	00781810736555
Material	Copper
Plating Type	Tin
UPC	781810736555

Logistics

Minimum Pack Quantity	50
Carton Quantity	600
Pallet Quantity	99999

Operational

Temperature Rating	105
--------------------	-----

Product Assets

[Catalog \[English\]](#)