



SP10BG25, Vinyl Splice For 12 - 10 AWG

By Burndy
Catalog # [SP10BG25](#)



Vinyl Splice For 12 - 10 AWG

Features

- Splices are constructed of pure electrolytic copper
- Long butted seam with deep V groove inner serrations for optimum conductivity, reliability, and holding power after crimping
- Designed for joining two wires securely
- Provides maximum conductivity, low resistance, and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion
- 600 Volts maximum, 105° C maximum

Application

For Accommodating A Broad Range Of 600 Volt Cables

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL467
Certification - CSA Approved	Yes
UL Listed	Yes
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor Size	12 - 10 AWG
Conductor - Copper Str Size	• 12 AWG • 10 AWG
Conductor - Copper Str Size Range	12 - 10 AWG

Configuration

Connector Type	Seamless Butt Splice
----------------	----------------------

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Package Height	0.000 in
Dimension - Strip Length inch	21/64 in
Dimension - Length Overall inch	1.23 in
Dimension - Diameter Max Size inch	0.26 in

General

Sub Brand	HYDENT
Insulation Type	Vinyl
Color Code	Yellow
Trade Name	VINYLINK™
Plated	Y
Feature - Barrel Style	Shrouded
Insulation	Y
Type	SP
UPC 12 Digit	781810486276
UPC 14 Digit GTIN	00781810486276
Material	Copper
Plating Type	Tin
UPC	781810486276

Logistics

Minimum Pack Quantity	5
Carton Quantity	5
Pallet Quantity	12000

Operational

Temperature Rating	105° C
--------------------	--------

Product Assets

[Catalog \[English\]](#)