




SP14, Vinyl Splice For 16 - 14 AWG

By Burndy
Catalog # [SP14](#)

Vinyl Splice For 16 - 14 AWG



Features

- Manufactured from seamless electrolytic copper tubing to provide maximum conductivity and tensile strength in a high quality design with no seams to split
- Funnel entry for easy wire insertion
- Electro-tin plating provides durable, long lasting resistance to corrosion

Application

For Accommodating A Broad Range Of 600 Volt Cables

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	16 - 14 AWG
Conductor - Copper Solid Size	• 16 AWG • 15 AWG • 14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor - Copper Str Size	16 - 14 AWG
Conductor - Copper Str Size Range	
Conductor - Copper Str Size	• 16 AWG • 14 AWG

Configuration

Connector Type	Seamless Butt Splice
----------------	----------------------

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	25 mm
Dimension - Outside Diameter	0.18 in
Dimension - Diameter Max Size	0.18 in
Dimension - Length Overall	1.00 in
Cable Insulation Diameter	0.180 in
Maximum	
Dimension - Strip Length inch	1/4 in

General

Feature - Barrel Style	Shrouded
Plated	Y
Color Code	Blue
Insulation Type	Polyvinylchloride
Trade Name	VINYLINK™
Sub Brand	VINYLINK
UPC	781810712016
Type	SP
Insulation	Y
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810712016
UPC 14 Digit GTIN	00781810712016

Logistics

Pallet Quantity	99999
Carton Quantity	600

Operational

Temperature Rating	105° C
--------------------	--------

Product Assets

[Catalog \[English\]](#)