

T1414, Uninsulated Ring Terminal For 16 - 14 AWG

By Burndy
Catalog # [T1414](#)

Uninsulated Ring Terminal For 16 - 14 AWG



Features

- Constructed of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Long brazed seam barrel and deep V groove inner serrations provide optimal conductivity, reliability and holding power after crimping
- Wire range is clearly marked on terminal for easy identification
- Long neck terminal permits easy bending and stacking of several terminals on a common stud

Application

For Control Wiring And Other Standard Duty Applications

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	16 - 14 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor Range	#20 AWG to #14 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Dimension - Pad Width inch	0.45 in
Package Height	0.000 in
Dimension - Hole Size fraction	17/63
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	24
Dimension - Hole Size inch	0.27 in
Dimension - Strip Length inch	9/32
Dimension - Stud Size inch	1/4 in
Dimension - Bolt Size fraction	1/4
Dimension - B Length fraction	13/50 in
Dimension - Z inch	0.47 in
Dimension - B Length inch	0.26 in
Dimension - Diameter Max Size inch	0.08 in
Dimension - Length Overall inch	0.95 in

General

Trade Name	HYLUG™
Feature - Barrel Type	Long
Plated	Y
Physical Attribute - Tongue Type	Ring
Sub Brand	HYLUG
UPC	781810722480
Type	Ring Tongue
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810722480
UPC 14 Digit GTIN	00781810722480

Logistics

Pallet Quantity	99999
Carton Quantity	1200

Product Assets

[Catalog \[English\]](#)