

Substation - Connector

By Burndy
Catalog # [NS22A22A](#)

Al Bolted Coupler, Connection Type: Al Tube To Tube, Tube Size:
4 IPS, Bolt Dia.:5/8 IN



Application

Substation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Tube Std Run Range	4 IPS
Conductor - AL Tube Std Run	4 IPS
Conductor - Connection Combination	Tube to Tube
Conductor - AL Tube Std Tap Range	4 IPS
Conductor - AL Tube Std Tap	4 IPS
Conductor Type	• AL Tube Std-Size • CU Tube Std-Size

Configuration

Physical Attribute - Pad Orientation	Straight
Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Number of Run Conductors	1
Connector Type	Couplers

Dimensions

Dimension - Height mm	150.9 mm
Dimension - Height inch	5.94 in
Dimension - L Length Overall mm	305 mm
Dimension - Width mm	168 mm
Dimension - Width inch	6.62 in
Dimension - Length Overall inch	12.00 in

Force Related

Installation Torque Recommended in-lb	480 LBS/in
---------------------------------------	------------

General

Material - Hardware	Aluminum
One Wrench Installation	Y
Plated	N
UPC	781810004357
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810004357
UPC 14 Digit GTIN	00781810004357

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)