


Substation - Connector

By Burndy
Catalog # [NT1414](#)



Cu Alloy T Connector, 4.13 IN L, 2.44 IN W, Tube to Tube, 3/4 IN IPS (Run), 3/4 IN IPS (Tap), 3/8 IN Bolt Size

Application

Substation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Connection Combination	Tube to Tube
Conductor - Copper Tube Std Tap Range	3/4 IPS
Conductor - Copper Tube Std Tap	3/4 IPS
Conductor Type	• CU Tube Std-Run • CU Tube Std-Tap
Conductor - Copper Tube Std Run Range	3/4 IPS
Conductor - Copper Tube Std Run	3/4 IPS

Configuration

Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Number of Run Conductors	1
Connector Type	T-Connector

Dimensions

Package Height	0.000 in
Dimension - Height mm	49.3 mm
Dimension - Height inch	1.94 in
Dimension - Height fraction	2 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	105 mm
Dimension - B Length fraction	2 in
Dimension - Width mm	62 mm
Dimension - Width inch	2.44 in
Dimension - B Length inch	2.00 in
Dimension - Length BB inch	2.00 in
Dimension - Length Overall inch	4.13 in

General

Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Plated	N
UPC	781810002599
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810002599
UPC 14 Digit GTIN	00781810002599

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)