



T144, Uninsulated Ring Terminal For 16 - 14 AWG

By Burndy
Catalog # [T144](#)



Uninsulated Ring Terminal For 16 - 14 AWG

Features

- Constructed of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Long brazed seam barrel and deep V groove inner serrations provide optimal conductivity, reliability and holding power after crimping
- Wire range is clearly marked on terminal for easy identification
- Long neck terminal permits easy bending and stacking of several terminals on a common stud

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor Size	16 - 14 AWG
Conductor Type	- CU C Solid-Size - CU C Str-Size
Conductor Range	#20 AWG to #14 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Package Length	0.000 in
----------------	----------

Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Z inch	0.28 in
Dimension - L Length Overall mm	17
Dimension - Pad Width inch	0.25 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/25
Dimension - Bolt Size fraction	#3 - #4
Dimension - Hole Size inch	0.12 in
Dimension - Strip Length inch	9/32
Dimension - Stud Size inch	#3 - #4
Dimension - Length Overall inch	0.66 in

General

Physical Attribute - Tongue Type	Ring
Trade Name	HYLUG™
Plated	Y
Feature - Barrel Style	Chamfered
Type	Ring Tongue
UPC 12 Digit	781810722329
UPC 14 Digit GTIN	00781810722329
Material	Copper
Plating Type	Tin
UPC	781810722329

Logistics

Minimum Pack Quantity	100
Carton Quantity	1200
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)