


Substation - Connector

By Burndy
Catalog # [NT1616](#)

Cast Cu Alloy T Connector, 5.69 IN, 3.50 IN W, Bolted, Tube to Tube, 1-1/4 IN IPS (Run), 1-1/4 IN IPS (Tap), 1/2 IN-13 Bolt Size



Application

Substation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Connection Combination	Tube to Tube
Conductor - Copper Tube Std Tap Range	1 1/4 IPS
Conductor - Copper Tube Std Tap	1 1/4 IPS
Conductor Type	• CU Tube Std-Run • CU Tube Std-Tap
Conductor - Copper Tube Std Run Range	1 1/4 IPS
Conductor - Copper Tube Std Run	1 1/4 IPS

Configuration

Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Number of Run Conductors	1
Connector Type	T-Connector

Dimensions

Package Height	0.000 in
Dimension - Height mm	66.8 mm
Dimension - Height inch	2.63 in
Dimension - Height fraction	2-5/8 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	145 mm
Dimension - B Length fraction	2-3/4 in
Dimension - Width mm	89 mm
Dimension - Width inch	3.50 in
Dimension - B Length inch	2.69 in
Dimension - Length BB inch	2.69 in
Dimension - Length Overall inch	5.69 in

General

Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Plated	N
UPC	781810002650
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810002650
UPC 14 Digit GTIN	00781810002650

Logistics

Pallet Quantity	32
Carton Quantity	2

Product Assets

[Catalog \[English\]](#)