



TN1014, Nylon Ring Terminal For 12 - 10 AWG

By Burndy
Catalog # [TN1014](#)

Nylon Ring Terminal For 12 - 10 AWG



Features

- Integral one-piece copper barrel/insulation grip and wire strain relief design for improved physical strength characteristics over a multi-piece design
- Pure electrolytic copper provides maximum conductivity, low resistance and ductility for excellend crimp forming properties
- Brazed seam provides a strong barrel design, minimized possible splitting and eliminates folding
- Deep inner bare serrations and smooth funnel entry provide excellent conductivity and pullout strength values with easy wire insertion
- Color-coded and clearly marked for quick easy wire size identification

Application

For Heavy Duty Industrial, Utility And Military Power And Control-Circuit Applications

Specifications

Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	UL486
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor Size	12 - 10 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor Range	#12 AWG to #10 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Current



A Hubbell brand

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	34 mm
Dimension - Pad Width inch	0.53 in
Package Height	0.000 in
Dimension - Strip Length inch	11/32 in
Dimension - Stud Size inch	• #12 • 1/4
Dimension - Z inch	0.37 in
Dimension - Bolt Size fraction	#12 - 1/4
Cable Insulation Diameter Maximum	0.21 in
Dimension - Length Overall inch	1.32 in

General

Insulation Type	Nylon
Trade Name	INSULUG™
Insulation	Y
Military Specification	MS25036
Sub Brand	INSULUG
Color Code	Yellow
Physical Attribute - Tongue Type	Ring
Plated	Y
Type	Ring Tongue
UPC 14 Digit GTIN	00781810734209
Material	Copper
Plating Type	Tin - Electro Plated
UPC	781810734209

Logistics

Minimum Pack Quantity	50
Carton Quantity	600
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)