



TN106BF, Nylon Block Fork Terminal For 12 - 10 AWG

By Burndy
Catalog # [TN106BF](#)

Nylon Block Fork Terminal For 12 - 10 AWG



Features

- Permits rapid and easy installation of the terminal under the screw head without complete removal of the screw

Application

Power Connector

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor Size	12 - 10 AWG
Conductor Type	- CU C Solid-Size - CU C Str-Size
Conductor Range	#10 AWG to #12 AWG

Configuration

Connector Type	Block Fork Terminal
----------------	---------------------

Dimensions

Dimension - Z inch	0.29 in
--------------------	---------

Dimension - L Length Overall mm	26 mm
Dimension - Pad Width inch	0.30 in
Dimension - Bolt Size fraction	#4 - #6
Dimension - Strip Length inch	3/8
Dimension - Stud Size inch	#4 #5 #6
Dimension - Length Overall inch	1.02 in

General

Sub Brand	HYDENT
Insulation Type	Nylon
Physical Attribute - Tongue Type	Fork
Trade Name	HYDENT™
Plated	Y
Insulation	Y
Type	Fork Tongue
UPC 14 Digit GTIN	00781810524121
Material	Copper
Plating Type	Tin - Electro Plated
UPC	781810524121

Logistics

Minimum Pack Quantity	50
Carton Quantity	100
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)