




TN108LF, Nylon Locking Fork Terminal For 12 - 10 AWG

By Burndy
Catalog # [TN108LF](#)



Nylon Locking Fork Terminal For 12 - 10 AWG

Features

- Locking fork tongue design allows fast installation - screw only has to be loosened for termination
- Internal configuration of the fork prevents the terminal from coming off the screw without applying a pulling force
- Locking fork is made from a copper alloy and permits many installations while maintaining proper spring retention of forks

Application

Power Connector

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor Size	12 - 10 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor Range	#10 AWG to #12 AWG

Configuration

Connector Type	Locking Fork Terminal
----------------	-----------------------

Dimensions

Package Length	5.750 in
----------------	----------

Package Width	3.600 in
Package Weight	0.190 lb.
Dimension - Z inch	0.29 in
Dimension - L Length Overall	26 mm
Dimension - Pad Width inch	0.33 in
Package Height	0.900 in
Dimension - Bolt Size fraction	#6 - #8
Dimension - Strip Length inch	11/32
Dimension - Stud Size inch	• #6 • #8
Dimension - Length Overall	1.02 in

General

Sub Brand	HYDENT
Insulation Type	Nylon
Physical Attribute - Tongue	Fork
Type	
Trade Name	INSULUG™
Plated	Y
Insulation	Y
Type	TN
UPC 14 Digit GTIN	00781810524152
Material	Copper
Plating Type	Unplated
UPC	781810524152

Logistics

Minimum Pack Quantity	1
Carton Quantity	100
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)



A Hubbell brand