



Full Cycle Ratchet Crimper, Dieless, Service Entrance

By Burndy
Catalog # [OH25](#)

Full Cycle Ratchet Crimper, Dieless, 6K lbs max force, Service Entrance
Splice Connectors #10 - #1/0 Str.

Features

- Heat treated steel
- 1/4" hole for snap fastener
- Forged steel jaws
- Nest die
- Comfort grip handles
- Spring loaded handles
- Protected ratchet mechanism
- Replacement stainless steel indenter

Application

Crimping

Specifications

Standards - RoHS Compliance EX
Status

Conductor

Crimping Ranges Aluminum: #10 AWG - #1/0 AWG

Dimensions



Length	12 in
Weight	2.687 lb.
Height	6.25 in
Width	0.75 in
Dimensions	12 in x 0.75 in x 6.25 in

General

Application - For Use On	Service Entrance Splices
Trade Name	HYTOOL™
Tool Type	Full Cycle Ratchet Crimper, Dieless
Product Type	OH and OUR Series
Die Type	Dieless
UPC	781810452004
UPC 12 Digit	781810452004
UPC 14 Digit GTIN	00781810452004

Logistics

Package Contents	Tool only
------------------	-----------

Product Assets

[Catalog \[English\]](#)