



PENA135GAL, Oxide Inhibitor, 5 Gallon

By Burndy
Catalog # [PENA135GAL](#)

Sealing Compound, Viscosity: 250 At 100 DEG F, Size: 5 GAL,
Container: Pail



Features

- PENETROX™ Oxide Inhibiting Joint Compounds are available in many types
- PENETROX A is a natural compound recommended for aluminum to aluminum, aluminum to copper connections and aluminum conduit threads, it is not recommended for use with rubber or polyethylene insulated conductors
- PENETROX A13 is a synthetic base compound with evenly suspended zinc particles recommended for aluminum to aluminum, aluminum to copper, and also aluminum conduit threads
- PENETROX E is a synthetic base with evenly suspended copper particles, recommended for copper to copper, copper threads, and all grounding applications

Application

For Aluminum To Copper, Aluminum To Aluminum, Aluminum To Conduit

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	Yes

Buy America(n) Qualified

Contact Manufacturer

General

Sub Brand	PENETROX
Trade Name	PENETROX™
Application - For Use On	- Aluminum to Aluminum - Aluminum to Conduit - Aluminum to Copper
Pour Point	-40 °F
Type	A13
UPC 12 Digit	781810033234
UPC 14 Digit GTIN	00781810033234
Container Type	Pail
UPC	781810033234

Logistics

Minimum Pack Quantity	1
Container Size	5 Gallon
Carton Quantity	1
Pallet Quantity	360

Operational

Temperature - Dropping Point	350 °F
Fahrenheit	
Viscosity at 100 Fahrenheit	250 °F

Product Assets

[Catalog \[English\]](#)