



Q2A312N, 2-Conductor, 2-Hole, Heavy Duty Copper Lug

By Burndy
Catalog # [Q2A312N](#)



2-Conductor, 250-350 kcmil, 2-Hole, 1/2" Stud, 1.75" Spacing, Compact Design

Features

- QIKLUG™ Terminals feature compact size, high copper alloy terminal for joining cables to equipment pads or bars
- Each element accommodates a wide range of cable
- One-wrench installation

Application

For Copper Cable

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	EX
Status	
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 250 kcmil • 300 kcmil • 350 kcmil
Conductor Size	250-350 kcmil
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	250 kcmil-350 kcmil

Configuration

Physical Attribute - Number of Screws	2
Physical Attribute - Number of Holes	2
Connector Type	Dual Clamp

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Dimension - Pad Width inch	2.69 in
----------------------------	---------

Package Height	0.000 in
Dimension - Height mm	42.9 mm
Dimension - Hole Size fraction	9/16
Dimension - Height inch	1.69 in
Dimension - Height fraction	1-11/16 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	0.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	114 mm
Dimension - Width fraction	2-1/8 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Stud Size inch	1/2
Dimension - Bolt Size fraction	1/2
Dimension - Width inch	2.13 in
Dimension - B Length inch	1.19 in
Dimension - D inch	3.09 in
Dimension - N inch	0.63 in
Dimension - Length Overall inch	4.44 in

Force Related

Installation Torque Recommended	325 LBS/in in-lb
---------------------------------	------------------

General

Product Family	MECHANICAL
Trade Name	QIKLUG™
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	No
Sub Brand	QIKLUG
Product Type	Terminal
UPC	781810321560
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810321560
UPC 14 Digit GTIN	00781810321560

Logistics

Minimum Pack Quantity	1
Pallet Quantity	720
Carton Quantity	6

Operational

[Catalog \[English\]](#)

[Installation Manual \[English\]](#)



A Hubbell brand